




REV	DESCRIPTION	ECN #	CHG BY	DATE	APP'D
A	ADDED GASKET/CONVERTED TO 3D	-	EZR	01/03/18	TAS
B	REMOVED ELEMENT TABLE	-	JEB	03/07/18	M.S
C	REMOVED GASKET	18331	TAS	02/07/20	NAD
D	ADDED RED SILICONE GASKET	DCR179	AMZ	06/06/24	NAS



SOLBERG®
Filtration • Separation • Silencing
 630.773.1363 • www.solbergmfg.com

THE INFORMATION CONTAINED HEREIN IS CONFIDENTIAL AND THE PROPERTY OF SOLBERG MANUFACTURING INC. AND IT IS FURNISHED TO YOU WITH THE EXPRESS UNDERSTANDING THAT IT WILL NOT BE REPRODUCED, COPIED IN ANY MANNER, LOANED OR OTHERWISE TRANSFERRED TO OTHERS ENTIRELY OR IN PART, NOR USED FOR ANY PURPOSE OTHER THAN FOR WHICH IT WAS FURNISHED. IT WILL BE RETURNED UPON REQUEST TO SOLBERG MANUFACTURING INC. THE ABOVE RESTRICTION IS IN ADDITION TO, AND DOES NOT IN ANY WAY ALTER, ANY OTHER RESTRICTIONS WHICH MAY APPLY TO THE INFORMATION CONTAINED HEREIN.

TOLERANCES
 DIMENSIONS ARE FOR REFERENCE ONLY. ALL DIMENSIONS ARE SUBJECT TO CHANGE UPON PRODUCTION.
 UNLESS OTHERWISE SPECIFIED:
 -DIMENSIONS ARE IN INCHES
 -REF: APPROXIMATE DIMENSIONS, NO TOLERANCES APPLY
 -FINISH: BREAK EDGES TO .005-.020 RADIUS/CHAMFER

MODEL NUMBER: CEG474/2

DESCRIPTION: CEG474/2, CEG COALESCING, HI-TEMP BROWN PLASTISOL, RED SILICONE

PROJECT:
SD21418

DRAWN BY: TAS
DATE: 8/18/2015

APPROVED BY: CCS
DATE: 8/18/2015

SHEET:
1 OF 1

REV:
D